

## Rosen Aviation Capability List

**ELECTRONIC REVISION  
CONTROLLED**

### LIMITED RADIO ARTICLE

| Part Number     | Description                |
|-----------------|----------------------------|
| 0700-001 MOD 00 | Headphone Distribution Amp |

### LIMITED ACCESSORY ARTICLES

| Part Number      | Description  |
|------------------|--|
| 0100-002         | Base Receptacle, Micro-D Standard                                  |
| 0100-004         | Base Receptacle, SlimLine, DB9 Harness, RNVAP Footprint            |
| 0100-010         | Base Receptacle, RNVAP   |
| 0100-015         | Base Receptacle, SlimLine POGO, BNC/Molex Harness, Small Footprint |
| 0100-041         | Base Receptacle, POGO DB 9 Harness                                 |
| 0100-042         | Base Receptacle, POGO  |
| 0100-043         | Base Receptacle, SlimLine Round POGO                               |
| 0100-044 MOD 00  | Base Receptacle, SlimLine POGO, DB9 Harness, RNVAP Footprint       |
| 0100-137 MOD 00  | SDI Base, G250   |
| 0100-138 MOD 00  | SDI Base, Right, G250  |
| 0100-139 MOD 00  | SDI Base, Left, G280   |
| 0100-140 MOD 00  | SDI Base, Right, G280  |
| 0100-202 MOD 00  | SDI Base   |
| 0100-211H MOD 00 | Base Receptacle, Micro-D Ethernet, Universal                       |
| 0100-302 MOD 00  | Base Receptacle, SDI, MCX  |
| 0100-342 MOD 00  | SDI Base, RS 232   |
| 0100-343 MOD 00  | Base Assembly, Round, SDI  |
| 0300-412 MOD 00  | RosenView Briefing Controller                                      |
| 0300-412 MOD 01  | RosenView Briefing Controller                                      |
| 0300-413 MOD 00  | VIP Controller   |
| 0300-414 MOD 00  | VIP Controller   |
| 0300-420 MOD 00  | Cabin Briefing Controller  |
| 0300-421 MOD 00  | Cabin Briefing Controller  |
| 0600-001         | Passenger Information System                                       |
| 0600-001 MOD 01  | Passenger Information System                                       |
| 0601-001 MOD 00  | DVD Player   |
| 0601-001 MOD 01  | DVD Player   |
| 0602-001 MOD 00  | Blu-ray DVD Player   |
| 0602-001 MOD 03  | Blu-ray DVD Player   |
| 0602-002 MOD 00  | Blu-ray DVD Player w/SDI   |
| 0602-002 MOD 01  | Blu-ray DVD Player w/SDI   |
| 0602-200 MOD 01  | Dual Blu-ray DVD Player, Bus Encryption                            |
| 0602-200 MOD 03  | Dual Blu-ray DVD Player, Bus Encryption                            |
| 0602-201 MOD 00  | Dual Blu-ray DVD Player w/Media Share (Rosen)                      |
| 0602-205 MOD 00  | Dual Blu-ray DVD Player w/Media Share                              |

## Rosen Aviation Capability List

| Part Number      | Description                                  |
|------------------|--|
| 0602-205 MOD 01  | Dual Blu-ray DVD Player w/Media Share        |
| 0602-205 MOD 02  | Dual Blu-ray DVD Player w/Media Share        |
| 0603-001 MOD 00  | RosenView LX                                 |
| 0603-001 MOD 01  | RosenView LX                                 |
| 0603-001 MOD 02  | RosenView LX                                 |
| 0603-001 MOD 03  | RosenView LX                                 |
| 0603-001 MOD 04  | RosenView LX                                 |
| 0603-001 MOD 05  | RosenView LX                                 |
| 0603-001 MOD 06  | RosenView LX                                 |
| 0603-001 MOD 07  | RosenView LX                                 |
| 0603-003 MOD 01  | RosenView MX                                 |
| 0603-003 MOD 02  | RosenView MX                                 |
| 0604-001 MOD 00  | RosenView VX                                 |
| 0604-001 MOD 01  | RosenView VX                                 |
| 0604-001 MOD 02  | RosenView VX                                 |
| 0604-001 MOD 03  | RosenView VX                                 |
| 0604-001 MOD 04  | RosenView VX                                 |
| 0604-003 MOD 00  | RosenView VX                                 |
| 0700-004 MOD 00  | SDI - DVI Converter                          |
| 0700-006 MOD 00  | Video Distribution Amplifier                 |
| 0700-006 MOD 01  | Video Distribution Amplifier                 |
| 0700-100 MOD 00  | Remote Monitor Electronics Box (RMEB)        |
| 0700-101 MOD 00  | Remote Monitor Electronics Box (RMEB)        |
| 0700-102H MOD 00 | Ovation Select, HD Scalar                    |
| 0700-103 MOD 00  | Remote Monitor Electronics Box (RMEB)        |
| 0700-104 MOD 00  | Remote Monitor Electronics Box (RMEB)        |
| 0700-104 MOD 01  | Remote Monitor Electronics Box (RMEB)        |
| 0700-105 MOD 01  | Remote Monitor Electronics Box (RMEB)        |
| 0700-107 MOD 00  | Remote Monitor Electronics Box (RMEB)        |
| 0700-107 MOD 01  | Remote Monitor Electronics Box (RMEB)        |
| 0700-107 MOD 02  | Remote Monitor Electronics Box (RMEB)        |
| 0700-108H MOD 00 | Ovation Select, HD Scalar                    |
| 0700-150 MOD 02  | Remote Monitor Electronics Box (RMEB), Smart |
| 0700-150 MOD 03  | Remote Monitor Electronics Box (RMEB), Smart |
| 0700-150 MOD 04  | Remote Monitor Electronics Box (RMEB), Smart |
| 0700-150 MOD 05  | Remote Monitor Electronics Box (RMEB), Smart |
| 0700-200 MOD 00  | Media Port w/Composite                       |
| 0700-202 MOD 00  | Media Port w/HDMI                            |
| 0700-203 MOD 00  | Media Port w/Composite                       |
| 0800-300 MOD 00  | Data Switch Unit                             |

## Rosen Aviation Capability List

| Part Number     | Description  |
|-----------------|--|
| 0800-400 MOD 00 | Passenger Control Unit, Ultra-CMS                  |
| 0800-500 MOD 00 | Media Decoder Unit, Ultra-CMS                      |
| 0801-100 MOD 00 | Media Encoder Unit, Ultra-CMS                      |
| 0801-400 MOD 00 | Passenger Control Unit, Ultra-CMS                  |
| 1040-005        | 10.4" LCD Monitor w/Bottom Pigtail                 |
| 1040-006        | 10.4" LCD Monitor w/C1 Cessna Connector            |
| 1040-080        | 10.4" LCD Monitor on Arm                           |
| 1041-120        | 10" NEC LCD Monitor on Gooseneck Arm - Left        |
| 1041-121        | 10" NEC LCD Monitor on Gooseneck Arm - Right       |
| 1042-001        | 10.4" Bulkhead w/Membrane                          |
| 1042-004 MOD 00 | 10.4" Bulkhead Ext BOT EXIT, ROSEN WHITE           |
| 1042-005        | 10.4" Bulkhead Ext Control                         |
| 1042-007        | 10.4" Bulkhead w/Membrane Auto On                  |
| 1042-010        | 10.4" LCD Monitor W/Falcon Arm                     |
| 1042-020        | 10.4" Monitor w/Falcon arm, ext plug               |
| 1042-021        | 10.4" Slimline Monitor With 10" Arm, Extended Plug |
| 1042-120        | 10.4" Monitor with Left Gooseneck                  |
| 1042-121        | 10.4" Monitor with Right Gooseneck                 |
| 1042-229        | 10.4" Monitor on Manual Lift                       |
| 1042-229 MOD 01 | 10.4" Monitor on Manual Lift                       |
| 1042-320        | 10.4" Monitor, Left Mount w/Tilt and Swivel        |
| 1042-321        | 10.4" Monitor, Right Mount w/Tilt and Swivel       |
| 1043-005 MOD 01 | 10.4" Bulkhead Monitor                             |
| 1043-005 MOD 02 | 10.4" Bulkhead Monitor                             |
| 1043-010 MOD 01 | 10.4" Monitor, 5XP Arm                             |
| 1043-020 MOD 00 | 10.4" Monitor with Falcon PCP Arm                  |
| 1043-020 MOD 01 | 10.4" Monitor, PCP Arm                             |
| 1043-037 MOD 00 | 10.4" Monitor, PCR POGO Locking Arm                |
| 1043-037 MOD 01 | 10.4" Monitor, PCR POGO Locking Arm                |
| 1043-037 MOD 02 | 10.4" Monitor, PCR POGO Locking Arm                |
| 1043-120 MOD 01 | 10.4" Monitor with Left Gooseneck                  |
| 1043-121 MOD 00 | 10.4" Monitor with Right Gooseneck                 |
| 1043-121 MOD 01 | 10.4" Monitor with Right Gooseneck                 |
| 1043-220 MOD 00 | 10.4" Monitor, Falcon Arm, Extended Plug           |
| 1043-260 MOD 00 | 10.4" Monitor, Left, SDI                           |
| 1043-261 MOD 00 | 10.4" Monitor, Right, SDI                          |
| 1043-30X MOD 01 | 10.4" Fold Down Monitor                            |
| 1060-001 MOD 00 | 10.6" HD Widescreen Bulkhead AIO                   |
| 1200-128 MOD 01 | 12" WS Monitor, Left Arm Rest                      |
| 1200-128 MOD 02 | 12" WS Monitor, Left Arm Rest                      |

## Rosen Aviation Capability List

| Part Number      | Description                              |
|------------------|--|
| 1200-128 MOD 03  | 12" WS Monitor, Left Arm Rest            |
| 1200-129 MOD 01  | 12" WS Monitor, Right Arm Rest           |
| 1200-129 MOD 02  | 12" WS Monitor, Right Arm Rest           |
| 1200-129 MOD 03  | 12" WS Monitor, Right Arm Rest           |
| 1200-137 MOD 00  | 12" G250, SDI Arm                        |
| 1200-138 MOD 00  | 12" G280, SDI Arm                        |
| 1200-237 MOD 00  | 12" Monitor, Center, G150                |
| 1401-006         | 14" Monitor with bottom pigtail          |
| 1401-007         | 14" Monitor with bottom pigtail          |
| 1401-010         | 14" Monitor with back pigtail            |
| 1401-082         | 14" Monitor with CKC Arm                 |
| 1402-006         | 14" Display with bottom pigtail          |
| 1402-007         | 14" Display with bottom pigtail          |
| 1402-010         | 14" Display with bottom pigtail          |
| 1402-012         | 14" Display with bottom pigtail          |
| 1402-103         | 14" Monitor with CKC Arm                 |
| 1500-002         | 15" SlimLine Monitor                     |
| 1500-003         | 15" Bulkhead w/ Membrane                 |
| 1500-003 MOD 01  | 15" SlimLine II, Bulkhead                |
| 1500-083         | 15" Monitor on CKC Arm Center            |
| 1500-084         | 15" Monitor on CKC Arm                   |
| 1500-100         | 15" Swing Out                            |
| 1500-100 MOD 01  | 15" SLIMLINE II SWING-OUT                |
| 1500-200 MOD 00  | 15" Swing-Out with SDI                   |
| 1560-001 MOD 00  | 15.6" AIO Monitor                        |
| 1700-001         | 17" SlimLine Monitor, Bulkhead           |
| 1700-002         | 17" SlimLine II                          |
| 1700-002 MOD 01  | 17" Monitor Assembly                     |
| 1700-002 MOD 02  | 17" Monitor Assembly                     |
| 1700-002 MOD 03  | 17" Monitor Assembly                     |
| 1700-002 MOD 04  | 17" Monitor Assembly                     |
| 1700-002 MOD 06  | 17" Monitor Assembly                     |
| 1700-002 MOD 07  | 17" Monitor Assembly                     |
| 1700-003 MOD 00  | 17" Bulkhead Monitor                     |
| 1701-001         | 17" Widescreen Display                   |
| 1701-001 MOD 00  | 17" Widescreen Display                   |
| 1702-001 MOD 00  | 17.5" HD Widescreen                      |
| 1702-002H MOD 00 | 17.5" WS Monitor, Ovation Select Version |
| 1702-003 MOD 00  | 17.5" HD Widescreen                      |
| 1702-003 MOD 01  | 17.5" HD Widescreen                      |

## Rosen Aviation Capability List

| Part Number      | Description                                      |
|------------------|--|
| 1800-008         | 18" Monitor w/Bottom Pigtail                     |
| 1800-010         | 18" Monitor with Back Pigtail                    |
| 1801-007         | 18" SXGA Display with Back Panel Adjustment      |
| 1801-108         | 18" Monitor w/Bottom Pigtail                     |
| 1801-010         | 18" Display with Back Pigtail                    |
| 1801-011         | 18" Monitor w/Bottom Pigtail, CS                 |
| 1801-012         | 18" display w/back pigtail                       |
| 1900-001 MOD 00  | 19" AIO Monitor                                  |
| 1900-001 MOD 01  | 19" WS Monitor                                   |
| 1900-003 MOD 00  | 19" AIO Monitor                                  |
| 1900-003 MOD 01  | 19" AIO Monitor                                  |
| 1901-100 MOD 00  | 19" RDM W/S                                      |
| 1901-100 MOD 01  | 19" RDM W/S                                      |
| 1901-101 MOD 00  | 19" WS w/ Remote Electronics                     |
| 1901-111 MOD 00  | 19" WS Remote Display Monitor (RDM), HS          |
| 1901-201 MOD 00  | 19" Remote Display Monitor (RDM)                 |
| 1901-201 MOD 01  | 19" Remote Display Monitor (RDM)                 |
| 1901-901 MOD 00  | 19" Bezel  |
| 2000-006         | 20" Display with Bottom Pigtail                  |
| 2000-010         | 20" Monitor w/Back Pigtail                       |
| 2001-006         | 20" Display with Bottom Pigtail                  |
| 2001-007         | 20" Display with Bottom Pigtail, Constant Ground |
| 2001-012         | 20" Display w/Back Pigtail                       |
| 2002-001         | 20" SlimLine Monitor Bulkhead                    |
| 2002-002         | 20" SlimLine II Monitor                          |
| 2002-002 MOD 01  | 20" SlimLine II Monitor                          |
| 2002-002 MOD 02  | 20" SlimLine II Monitor                          |
| 2002-002 MOD 03  | 20" SlimLine II Monitor                          |
| 2002-251         | 20" SlimLine Display w/Motorized Lift            |
| 2002-501 MOD 02  | 20" SlimLine II, Lift RGB                        |
| 2201-100 MOD 00  | 22" Remote Display Monitor (RDM)                 |
| 2201-102H MOD 00 | 22" Remote Display Monitor (RDM)                 |
| 2400-001         | 24" Widescreen Monitor                           |
| 2401-001 MOD 02  | 24" Monitor                                      |
| 2401-003 MOD 00  | 24" Top Level Assembly DC                        |
| 2401-100 MOD 00  | 24" Remote Display Monitor (RDM)                 |
| 2401-201 MOD 00  | 24" Remote Display Monitor (RDM)                 |
| 2601-100 MOD 00  | 26" Remote Display Monitor (RDM)                 |
| 2601-100 MOD 01  | 26" Remote Display Monitor (RDM)                 |
| 2601-201 MOD 00  | 26" Remote Display Monitor W/S                   |

## Rosen Aviation Capability List

| Part Number       | Description  |
|-------------------|--|
| 2601-201 MOD 01   | 26" Remote Display Monitor W/S                       |
| 2601-201 MOD 02   | 26" Remote Display Monitor W/S                       |
| 2601-960 MOD 00   | Bezel, 26" W/S                                       |
| 3201-100 MOD 00   | Top Level Assembly, RDM 32" W/S                      |
| 3201-100 MOD 01   | 32" Remote Display Module (RDM)                      |
| 3201-102H MOD 00  | 32" Remote Display Module (RDM)                      |
| 3201-201 MOD 01   | 32" Remote Display Module (RDM)                      |
| 4201-100 MOD 00   | 42" RDM, ROSEN                                       |
| 4201-201 MOD 01   | 42" Remote Display Monitor W/S                       |
| 441-2028-100      | Remote Monitor Electronics Box (RMEB), Smart         |
| 441-2056-100      | 24" 4K Monitor                                       |
| 4KD240-300 MOD 00 | 24" 4K Monitor                                       |
| 5600-010          | 5.6" SlimLine Display and Arm / Center Mount         |
| 5600-020          | 5.6" SlimLine Display                                |
| 5600-030          | 5.6" SlimLine Display                                |
| 5600-040          | 5.6" Slimline Display w/Ext. Plug                    |
| 5600-060          | 5.6" SlimLine Display Left Mount                     |
| 5600-061          | 5.6" SlimLine Display Right Mount                    |
| 5600-080          | 5.6" SlimLine Display with RNVAP-5PLL Arm            |
| 5600-082          | 5.6" SlimLine, RNVAP, Left Mount                     |
| 5600-100          | 5.6" SlimLine Display w/Side Mount Arm               |
| 5600-120          | 5.6" SlimLine Display, Left Mount, 9" Gooseneck Arm  |
| 5600-121          | 5.6" SlimLine Display, Right Mount, 9" Gooseneck Arm |
| 5600-130          | 5.6" SlimLine Pedestal Mount                         |
| 5600-140          | 5.6" SlimLine Pedestal Mount 330°                    |
| 5600-161          | 5.6" SlimLine Sidewall Mount                         |
| 5600-163          | 5.6" SlimLine Display with Right Swing Out - Gray    |
| 5600-170          | 5.6" Slimline Display Cockpit Cabin Mount            |
| 5600-182          | 5.6" SlimLine Display, RNVAP 5PAB Arm, Left Mount    |
| 5600-183          | 5.6" SlimLine Display, RNVAP 5PAB Arm, Right Mount   |
| 5601-006          | 5.6" SlimLine Monitor Top Mount, Right               |
| 5601-010          | 5.6" SlimLine III Center Mount SXP                   |
| 5601-011          | 5.6" Display w/ POGO Arm                             |
| 5601-020          | 5.6" SlimLine Monitor w/Arm Assembly                 |
| 5601-021          | 5.6" SlimLine Monitor, PCP Arm, POGO                 |
| 5601-030          | 5.6" SlimLine Monitor w/ Arm Assembly                |
| 5601-033          | 5.6" SlimLine Display, SS PCR5                       |
| 5601-035          | 5.6" SlimLine, SS PCR5, POGO                         |
| 5601-036          | 5.6" Display w/ POGO Locking Arm                     |
| 5601-060          | 5.6" SlimLine Monitor w/ Arm Assembly                |

## Rosen Aviation Capability List

| Part Number     | Description  |
|-----------------|--|
| 5601-061        | 5.6" SlimLine Monitor w/ Arm assembly                      |
| 5601-081        | 5.6" SlimLine, ULL, Left Mount                             |
| 5601-100        | 5.6" SlimLine Display with Side Mount Arm                  |
| 5601-110        | 5.6" SlimLine Monitor w/ Flight Deck Mount Arm Assembly    |
| 5601-111        | 5.6" Display w/ POGO Arm Placard                           |
| 5601-130        | 5.6" Pedestal Mount 180 Rotation                           |
| 5601-161        | 5.6" SlimLine III Right, Sidwall Mount                     |
| 5601-165        | 5.6" Right Hand Sidewall Flight Deck Mount                 |
| 5601-170        | 5.6" SlimLine III CCM                                      |
| 5601-171        | 5.6" SlimLine III CCM w/logo                               |
| 5601-182        | 5.6" SlimLine III, UAB left mount, 12V                     |
| 5601-183        | 5.6" SlimLine III, UAB right mount, 12V                    |
| 5601-190        | 5.6" Slimline III, Falcon Arm, Extended                    |
| 6500-010        | 6.5" Slimline, Center, SXP5 Arm                            |
| 6500-010 MOD 01 | 6.5" Slimline, Center, SXP5 Arm                            |
| 6500-011        | 6.5" Center SXP6.5 POGO Arm                                |
| 6500-011 MOD 01 | 6.5 Slimline, Center, SXP5 POGO Arm                        |
| 6500-025        | 6.5" Slimline, PCP.2 POGO Arm                              |
| 6500-037        | 6.5" SlimLine, PCR5 Arm, POGO Pin                          |
| 6500-061        | 6.5" SlimLine, Right Mount, SLA Arm                        |
| 6500-080        | 6.5" SlimLine, Left Mount, ULL-L                           |
| 6500-081        | 6.5" SlimLine, Right Mount, ULL-R                          |
| 6500-111        | 6.5" Monitor Assembly, Center, SXP6.5 Arm, w/Select Switch |
| 6500-111 MOD 01 | 6.5" Monitor Assembly, Center, SXP6.5 Arm, w/Select Switch |
| 6500-127 MOD 01 | 6.5" SlimLine, Right, Gooseneck Arm                        |
| 6500-137 MOD 00 | 6.5" SlimLine, Locking PCR5 Arm, POGO Pin 4/5 Jumper       |
| 6500-182        | 6.5" SlimLine, Left Mount                                  |
| 6500-182 MOD 01 | 6.5" SlimLine, Left Mount, 12V, UAB                        |
| 6500-183        | 6.5" SlimLine, Right Mount                                 |
| 6500-184        | 6.5" SlimLine, Center, UAB Arm                             |
| 7000-010        | 7" WideScreen, Center, SXP5 Arm                            |
| 7000-011        | 7" WideScreen, Center Mount, SXP5 ARM, POGO                |
| 7000-013        | 7" WideScreen, Center Mount w/Select Switch                |
| 7000-015        | 7" WideScreen, Center Mount, Select Switch, POGO Arm       |
| 7000-030        | 7" WideScreen, Center, PCR Arm                             |
| 7000-035        | CENTER MOUNT w/SELECT SWITCH PCR5 ARM, POGO                |
| 7000-037        | 7" WideScreen, Center, Select Switch, PCR5 POGO Locking    |
| 7000-038        | 7" WideScreen, Center, 90° CCW PCR5 Locking POGO           |
| 7000-060        | 7" WideScreen, Left, SLA5 Left Arm                         |
| 7000-061        | 7" WideScreen, Right, SLA5 Right Arm                       |

## Rosen Aviation Capability List

| Part Number     | Description                                      |
|-----------------|--|
| 7000-111        | 7" WideScreen, Center, SXP5 POGO Arm             |
| 7000-181        | 7" WideScreen, Right, UAB5 Arm                   |
| 7001-001        | 7" WideScreen, Sidewall Mount                    |
| 7001-008        | 7" WideScreen, Sidewall Mount w/Select Switch    |
| 7001-009        | 7" WideScreen, Sidewall Mount w/Select Switch    |
| 7001-102 MOD 00 | 7" WideScreen, Sidewall Mount, Beige             |
| 7001-103 MOD 00 | 7" WideScreen, Sidewall Mount, Left, Beige, SS   |
| 7002-001 MOD 00 | 7" WideScreen, Bulkhead                          |
| 7002-013 MOD 00 | 7" WideScreen, Center, SXP Arm                   |
| 7002-015 MOD 00 | 7" WideScreen, Center, POGO                      |
| 7002-033 MOD 00 | 7" Wide Screen, Center, PCR                      |
| 7002-035 MOD 00 | 7" WideScreen, Center Mount, POGO                |
| 7002-037 MOD 00 | 7" WideScreen, Center, PCR5 180 Arm              |
| 7002-037 MOD 02 | 7" WideScreen, Locking Center Mount, POGO        |
| 7002-038 MOD 00 | 7" WideScreen, Center, PCR5 90 Arm               |
| 7002-040 MOD 00 | 7" WideScreen, Center, POGO                      |
| 7002-060 MOD 01 | 7" WideScreen, Left, 7002 Monitor, SLA5 Left Arm |
| 7002-061 MOD 01 | 7" WideScreen, Right, SLA5 Arm                   |
| 7002-065 MOD 00 | 7" WideScreen, Right Mount POGO                  |
| 7002-080 MOD 00 | 7" WideScreen, Left, ULL Arm                     |
| 7002-081 MOD 00 | 7" WideScreen, Right, ULL Arm                    |
| 7002-111 MOD 00 | 7" WideScreen, Center, POGO                      |
| 7002-126 MOD 00 | 7" WideScreen, Left, RGD9 Arm                    |
| 7002-127 MOD 00 | 7" WideScreen, Right, RGD9 Arm                   |
| 7002-260 MOD 00 | 7" WideScreen, SDI, Left, SLA5 Arm               |
| 7002-261 MOD 00 | 7" WideScreen, SDI, Right, SLA5 Arm              |
| 7002-320 MOD 00 | 7" WideScreen, Gooseneck, Left, SDI, RS232       |
| 7002-321 MOD 00 | 7" WideScreen, Gooseneck, Right, SDI, RS232      |
| 7002-360 MOD 01 | 7" Widescreen, SDI, Left                         |
| 7002-361 MOD 00 | 7" Widescreen, SDI, Right                        |
| 7002-361 MOD 01 | 7" Widescreen, SDI, Right                        |
| 7004-060 MOD 00 | 7" Composite, SLA5 Arm Mount, Left               |
| 7004-061 MOD 00 | 7" Composite, SLA5 Arm Mount, Right              |
| 7004-363 MOD 00 | 7" HD WS, RIGHT, SDI, RS232                      |
| 7006-001 MOD 00 | Galley Touch Screen                              |
| 7006-001 MOD 01 | Galley Touch Screen                              |
| 7006-001 MOD 02 | Galley Touch Screen                              |
| 8400-010        | 8.4" Display w/Arm                               |
| 8400-011        | 8.4" Display w/ Arm, POGO Pins                   |
| 8400-020        | 8.4" w/Ext Arm & Plug                            |



## Rosen Aviation Capability List

| Part Number     | Description  |
|-----------------|--|
| 8400-030        | 8.4" SlimLine LCD Monitor with Articulating Arm              |
| 8400-033        | 8.4" SlimLine LCD Monitor, Center Mount, Select Switch       |
| 8400-060        | 8.4" Display, w/Arm, Left                                    |
| 8400-061        | 8.4" Display, w/Arm, Right                                   |
| 8400-070        | 8.4" Display, w/Arm, Center                                  |
| 8400-121        | 8.4" Display, Right 3" Gooseneck Arm                         |
| 8400-124        | 8.4" Display, Left Gooseneck                                 |
| 8400-125        | 8.4" Display, Right Gooseneck                                |
| 8402-001        | 8.4" Bulkhead Monitor  |
| 8402-010        | 8.4" SlimLine III, Center Mount, SXP                         |
| 8402-011        | 8.4" SlimLine III, Center Mount, POGO                        |
| 8402-020        | 8.4" SlimLine III, Center Mount w/PCP Arm                    |
| 8402-021        | 8.4" SlimLine III, Center Mount, POGO                        |
| 8402-030        | 8.4" SlimLine III, Center Mount, PCR8 Arm                    |
| 8402-033        | 8.4" Slimline III, Center, SS, PCR8 Arm                      |
| 8402-035        | 8.4" SlimLine III, Center Mount, POGO, Select Switch         |
| 8402-037        | 8.4" SlimLine Monitor w/ Locking Arm Assembly                |
| 8402-039        | 8.4" SLIMLINE III, MONITOR, SS 90°CW PCR8 LOCKING POGO ARM   |
| 8402-060        | 8.4" Display w/Arm, Left                                     |
| 8402-061        | 8.4" Display w/Arm, Right                                    |
| 8402-111        | 8.4" SlimLine III Center SXP8 POGO Arm, Placard              |
| 8402-124        | 8.4" SlimLine III, 9" Gooseneck, Left                        |
| 8402-125        | 8.4" SlimLine III, 9" Gooseneck, Right                       |
| 8403-001        | 8.4" Monitor, Bulkhead Mount                                 |
| 8403-001 MOD 01 | 8.4" Monitor, Bulkhead Mount                                 |
| 8403-010        | 8.4" SlimLine IV, Center Mount, SXP                          |
| 8403-010 MOD 01 | 8.4" SlimLine IV, Center Mount, SXP                          |
| 8403-011        | 8.4" SlimLine IV, SXP POGO Arm                               |
| 8403-020 MOD 01 | 8.4" SlimLine IV, Center Mount, PCP8 Arm                     |
| 8403-030        | 8.4" SlimLine IV, Center Mount, PCR8 Arm                     |
| 8403-030 MOD 01 | 8.4" Monitor, Center Mount w/PCR8 Arm                        |
| 8403-034        | 8.4" SlimLine IV, Center Mount, PCR POGO Arm                 |
| 8403-037        | 8.4" SlimLine IV, Center Mount, PCR POGO Locking Arm         |
| 8403-037 MOD 01 | 8.4" MONITOR,CENTER MOUNT, w/LOCKING PCR8 POGO ARM           |
| 8403-038        | 8.4" SlimLine IV, 90° CCW PCR8 Locking Pogo Arm              |
| 8403-038 MOD 01 | 8.4" SlimLine IV, 90° CCW PCR8 Locking Pogo Arm              |
| 8403-039        | 8.4" SlimLine IV, Select Switch 90° CW PCR8 Locking Pogo Arm |
| 8403-040 MOD 00 | 8.4" SlimLine IV, w/Locking POGO PCR8 Arm, Brush Aluminum    |
| 8403-060 MOD 00 | 8.4" Slimline IV, Left Mount w/SLA8R Arm                     |
| 8403-061 MOD 01 | 8.4" Slimline IV, Right Mount w/SLA8R Arm                    |

## Rosen Aviation Capability List

| Part Number      | Description  |
|------------------|--|
| 8403-111         | 8.4" SlimLine IV, Center Mount, SXP POGO Arm, Placard  |
| 8403-111 MOD 01  | 8.4" SlimLine IV, Center Mount, SXP POGO Arm, Placard  |
| 8403-127         | 8.4" SlimLine IV, 9" Gooseneck Arm                     |
| 8403-127 MOD 01  | Top Level Assembly, 8.4" Monitor, Right, Gooseneck Arm |
| 9000-010 MOD 00  | 9" WS Center Mount                                     |
| 9000-037 MOD 00  | 9" WS Center, PCR5 Arm                                 |
| 9000-045H MOD 00 | 9" Center Monitor, Locking Arm                         |
| 9000-047H MOD 00 | 9" LCD Monitor Center, Non-Locking Arm                 |
| 9000-111 MOD 00  | 9" WS, Center Mount, POGO Arm, Placard                 |
| 9000-137 MOD 00  | 9" Display, G250 SDI Arm                               |
| 9000-138 MOD 01  | 9" Monitor, G280 SDI Arm                               |
| 9000-224 MOD 00  | 9" WS, Left, Gooseneck                                 |
| 9000-224 MOD 01  | 9" WS, Left, Gooseneck                                 |
| 9000-225 MOD 00  | 9" WS, Right, Gooseneck                                |
| 9000-225 MOD 01  | 9" WS Right, Gooseneck                                 |
| 9000-237 MOD 00  | 9" MONITOR, CENTER                                     |
| 9000-260 MOD 00  | 9" WS, Left, SDI, SLA Arm                              |
| 9000-261 MOD 00  | 9" WS, Right, SDI, SLA Arm                             |
| 9000-324 MOD 00  | 9" WS Monitor, Left, Gooseneck, RS232                  |
| 9000-325 MOD 00  | 9" WS Monitor, Right, Gooseneck, RS232                 |
| 9000-360 MOD 00  | 9" WS, Left, SDI, RS-232                               |
| 9000-361 MOD 00  | 9" WS, Right, SDI, RS-232                              |
| 9001901          | 20" SlimLine Display w/Motorized Lift                  |
| 9200-0102-005    | 10.4" LCD Monitor w/Bottom Pigtail                     |
| 9200-0102-006    | 10.4" LCD Monitor w/C1 Cessna Connector                |
| 9200-0102-080    | 10.4" LCD Monitor on Arm                               |
| 9200-0103-121    | 8.4" Display, Right 3" Gooseneck Arm                   |
| 9200-0106-010    | 20" Monitor w/Back Pigtail                             |
| 9200-0106-252    | 20" Monitor w/Bottom Pigtail, Constant Ground          |
| 9200-0106-256    | 20" Monitor w/Back Pigtail                             |
| 9200-0108-007    | 14" Display with bottom pigtail                        |
| 9200-0108-082    | 14" Monitor with CKC Arm                               |
| 9200-0108-310    | 14" Display with bottom pigtail                        |
| 9200-0109-008    | 18" Monitor w/Bottom Pigtail                           |
| 9200-0109-010    | 18" Monitor with Back Pigtail                          |
| 9200-0109-112    | 18" Display w/Back Pigtail                             |
| 9200-0109-108    | 18" Monitor w/Bottom Pigtail                           |
| 9200-0109-110    | 18" Display with Back Pigtail                          |
| 9200-0109-111    | 18" Monitor w/Bottom Pigtail, CS                       |
| 9200-0115-130    | 5.6" SlimLine Pedestal Mount                           |

## Rosen Aviation Capability List

| Part Number           | Description  |
|-----------------------|--|
| 9200-0115-140         | 5.6" SlimLine Pedestal Mount 330°                            |
| 9200-0116-002         | Slimline Base Receptacle / 28 Volt Configuration RSLM-5SB/28 |
| 9200-0116-004         | Slimline Base Receptacle / 28 Vdc                            |
| 990-E0890-005         | 9" LCD Monitor w/5.5" Locking Arm                            |
| 990-E0890-006         | 9" LCD Monitor w/5.5" Arm                                    |
| 990-E0890-045         | 9" Center Monitor, Locking Arm                               |
| 990-E0890-047         | 9" LCD Monitor Center, Non-Locking Arm                       |
| 990-E0891-001         | Base Receptacle, Universal Flange                            |
| 990-E0891-005         | Base Receptacle, Micro-D Ethernet                            |
| 990-E0891-211         | Base Receptacle, Universal Flange, HS                        |
| 990-E1010-001         | 10.1" Touchscreen (OST)                                      |
| 990-E1700-001         | 17.5" WS Monitor, Ovation Select Version                     |
| 990-E1900-001         | 19" WS Monitor, Ovation Select Version                       |
| 990-E1900-002         | RDM, 19" W/S, Male RJ-45                                     |
| 990-E2200-001         | 22" Remote Display Monitor (RDM)                             |
| 990-E2400-001         | 24" Remote Display Module (RDM)                              |
| 990-E3200-002         | 32" Remote Display Module (RDM)                              |
| 990-E4790-004         | Ovation Select, HD Scalar                                    |
| 990-E4790-108         | Ovation Select, HD Scalar                                    |
| CTS100-001 MOD 01     | 10.1" Touchscreen Control Panel                              |
| CTS100-102H MOD 00    | 10.1" Touchscreen (OST)                                      |
| RGD-9C-L/28           | 5.6" SlimLine Display, Left Mount, 9" Gooseneck Arm          |
| RGD-9C-R/28           | 5.6" SlimLine Display, Right Mount, 9" Gooseneck Arm         |
| RLCD14-5/28           | 14" VGA Monitor, 28V   |
| RLCD14-5B1/28         | 14" VGA Monitor, 28V Bottom Exit Harness                     |
| RLCD14-5-B1/28        | 14" VGA Monitor, 28V Bottom Exit Harness                     |
| RLCD14-6/28           | 14" Thinline Display, 28V                                    |
| RLCD14-6-B1/28        | 14" Thinline Display, Bottom Pigtail, 28V                    |
| RLCD14-7/28           | 14" Window Mount, 28V  |
| RLCD14-7-B1/28        | 14" Window Mount, 28V Bottom Exit Harness                    |
| RLCD14-8-B1/28        | 14" Monitor with bottom pigtail                              |
| RLCD14-8-B2/28        | 14" Monitor with back pigtail                                |
| RLCD14-8CKC-CS-WO/28  | 14" Monitor with CKC Arm                                     |
| RLCD14-8-CKC-CS-WO/28 | 14" Monitor with CKC Arm                                     |
| RLCD14-8-CS-B1/28     | 14" Monitor with bottom pigtail                              |
| RLCD18-6-AD-B1/28     | 18" Monitor w/Bottom Pigtail                                 |
| RLCD18-6-B1/28        | 18" Monitor w/Bottom Pigtail                                 |
| RLCD18-6-B1-AD/28     | 18" Monitor w/Bottom Pigtail                                 |
| RLCD18-6-B2/28        | 18" Monitor with Back Pigtail                                |
| RLCD20-6B-B1/28       | 20" Monitor w/Bottom Pigtail                                 |

## Rosen Aviation Capability List

| Part Number        | Description                                       |
|--------------------|---|
| RLCD20-6B-B2/28    | 20" Monitor w/Back Pigtail                        |
| RLCD6L-1MPM        | 5.6" Slimline Pedestal Mount                      |
| RLCD6L-1MPM/28     | 5.6" SlimLine Pedestal Mount                      |
| RLCD6L-1PMT/28     | 5.6" SlimLine Pedestal Mount 330°                 |
| RNVAP-5ULL-L/28    | 5.6" SlimLine w/left mount arm                    |
| RNVAP-5ULL-L-WO/28 | 5.6" SlimLine w/left mount arm                    |
| RNVAP-5ULL-R/28    | 5.6" SlimLine w/right mount arm                   |
| RNVAP-5ULL-R-WO/28 | 5.6" SlimLine w/right mount arm                   |
| RNVAP-5ULP-L-WO/28 | 5.6" SlimLine Display w/left mount arm            |
| RNVAP-5ULP-L/28    | 5.6" SlimLine Display w/left mount arm            |
| RNVAP-5UVK/28      | 5.6" SlimLine Display w/Side Mount Arm            |
| RNVAP-5UVK-WO/28   | 5.6" SlimLine Display w/Side Mount Arm            |
| RSLM-5CCM/28       | 5.6" SlimLine Display Cockpit Cabin Mount         |
| RSLM-5PCP-WO/28    | 5.6" SlimLine Display                             |
| RSLM-5PCR-WO/28    | 5.6" SlimLine Display                             |
| RSLM-5SA/28        | Slimline Base Receptacle / 28 Vdc                 |
| RSLM-5SB/28        | Slimline Base Receptacle / 28 Vdc                 |
| RSLM-5SLA-L/28     | 5.6" SlimLine Display and arm / left mount        |
| RSLM-5SLA-L-WO/28  | 5.6" SlimLine Display and arm / left mount        |
| RSLM-5SLA-R/28     | 5.6" SlimLine Display and arm / right mount       |
| RSLM-5SLA-R-WO/28  | 5.6" SlimLine Display and arm / right mount       |
| RSLM-5SLB-WO/28    | 5.6" Display w/Ext. Plug Slimline                 |
| RSLM-5SXP/28       | 5.6" SlimLine Display and arm / center mount      |
| RSLM-5SXP-WO/28    | 5.6" SlimLine Display and arm / center mount      |
| RSLM-5WTM-R/28     | 5.6" SlimLine Display with Right Swing Out        |
| RSLM-5WTM-R-118/28 | 5.6" SlimLine Display with Right Swing Out - Gray |
| RSLM84-1RGD-R/28   | 8.4" Display, Right 3" Gooseneck Arm              |
| RSLM84-1SXP-WO/28  | 8.4" Display                                      |
| SDM156-001 MOD 00  | 15.6" Smart Display Module                        |
| SDM185-001 MOD 00  | 18.5" Smart Bulkhead Display                      |
| SDM220-001 MOD 00  | 22" Smart Bulkhead Display                        |
| SDM220-111 MOD 00  | 22" Smart Display                                 |
| SDM240-201 MOD 00  | 24" Smart Bulkhead Display                        |
| SDM240-201 MOD 01  | 24" Smart Bulkhead Display                        |
| SDM260-001 MOD 00  | 26" Smart Bulkhead Display                        |
| SDM320-001 MOD 00  | 32" Smart Bulkhead Display                        |

## Rosen Aviation Capability List

| Revision History |  |                  |
|------------------|--|------------------|
| Revision         | Change(s) Made   | Change Authority |
| A                | Initial Release (Changed from Doc # 9002893)   | AC-14005         |
| B                | Add 1700-002 MOD 6   | AC-14006         |
| C                | Add 8403-039   | AC-14009         |
| D                | Add 990-E0891-001 and 990-E1900-002  | AC-14010         |
| F                | Add 2201-100 MOD 00  | AC-14012         |
| G                | Add 7002-361 MOD 00  | AC-14015         |
| H                | Add 2001-012/9200-0106-256 and 0100-211H MOD 00/990-E0891-211  | AC-14016         |
| J                | Add 2601-201 MOD 01  | AC-14022         |
| K                | Add 1200-138 MOD 00  | AC-14024         |
| L                | Add 0700-108H MOD 00 and 990-E4790-108   | AC-14025         |
| M                | Add 0100-139 MOD 00 and 0100-140 MOD 00  | AC-14026         |
| N                | Add 8402-021   | AC-14027         |
| P                | Add 1560-001 MOD 00  | AC-14028         |
| R                | Add 0700-107 MOD 01 and 1402-103   | AC-14032         |
| T                | Add 9200-0108-007  | AC-14033         |
| U                | Add 0700-001 MOD 00 and separate sections for Limited Radio and Limited Accessory  | AC-14036         |
| V                | Add 7001-103 MOD 00 to Limited Accessory   | AC-14037         |
| W                | Add 0603-003 MOD 01 to Limited Accessory   | AC-14039         |
| Y                | Remove 0801-500 MOD 00.<br>Add 0800-500 MOD 00, 2201-102H MOD 00, 1702-003 MOD 00, 7000-013, 9000-111 MOD 00 and 990-E2200-001 | AC-14040         |
| AA               | Add 7000-181   | AC-14042         |
| AB               | Add 0602-002 MOD 00  | AC-14043         |
| AC               | Add 1042-229 MOD 01, 1401-082, 9200-0108-082, RLCD14-8-CKC-CS-WO/28 and RLCD14-8CKC-CS-WO/28                                   | AC-15001         |
| AD               | Add 0604-003 MOD 00 and 1900-003 MOD 01  | AC-15002         |
| AF               | Add 7006-001 MOD 01  | AC-15005         |
| AG               | Add 9000-324 MOD 00, 9000-325 MOD 00 and RLCD14-5B1/28   | AC-15006         |
| AH               | Add 7004-060 MOD 00  | AC-15007         |
| AJ               | Add 0603-001 MOD 07, 0700-150 MOD 02 and 1500-200 MOD 00   | AC-15008         |
| AK               | Add 0602-200 MOD 01 and 0700-107 MOD 02  | AC-15011         |
| AL               | Add 9000-360 MOD 00  | AC-15012         |
| AM               | Add 7002-038 MOD 00 and 7002-321 MOD 00  | AC-15013         |
| AN               | Add 1702-003 MOD 01 and 9000-138 MOD 01  | AC-15014         |
| AP               | Add 1901-901 MOD 00  | AC-15016         |
| AR               | Add 6500-010 MOD 01 and 8402-020   | AC-15019         |
| AT               | Add 0300-420 MOD 00, 0700-150 MOD 03 and 1901-111 MOD 00   | AC-15022         |

## Rosen Aviation Capability List

| Revision History |   |                  |
|------------------|---|------------------|
| Revision         | Change(s) Made  | Change Authority |
| AU               | Add 7004-061 MOD 00   | AC-15023         |
| AV               | Add 6500-184  | AC-15025         |
| AW               | Add 0700-102H MOD 01, 1702-002H MOD 00, 9000-045H MOD 00, 990-E0890-045 and 990-E1700-001 | AC-15028         |
| AY               | Add 1043-020 MOD 01   | AC-15030         |
| BA               | Add RNVAP-5ULP-L-WO/28 and RNVAP-5ULP-L/28  | AC-15031         |
| BB               | Add 1043-121 MOD 01   | AC-15033         |
| BC               | Add 8403-038  | AC-15036         |
| BD               | Add 8403-040 MOD 00   | AC-15037         |
| BF               | Add 441-2028-100 Rev B and 441-2028-100 Rev C   | AC-15038         |
| BG               | Add 2001-007 and 9200-0106-252  | AC-15041         |
| BH               | Add 0700-150 MOD 04 and 441-2028-100 Rev D  | AC-15042         |
| BJ               | Add 2601-201 MOD 02 and 4201-201 MOD 01   | AC-16002         |
| BK               | Add 0700-203 MOD 00 and 8403-001 MOD 01   | AC-16003         |
| BL               | Add 0602-205 MOD 02   | AC-16012         |
| BM               | Remove Rev reference of 441-2028-100 from Capability List                                 | AC-16014         |
| BN               | Add 7002-001 MOD 00   | AC-16017         |
| BP               | Add 8403-038 MOD 01   | AC-16018         |
| BR               | Add 7006-001 MOD 02   | AC-16019         |
| BT               | Add 1040-080 and 9200-0102-080  | AC-16020         |
| BU               | Add 1801-008 and 9200-0109-108  | AC-16022         |
| BV               | Add 0100-044 MOD 00 and 8403-001  | AC-16026         |
| BW               | Add 1200-128 MOD 02 and 1200-129 MOD 02   | AC-16029         |
| BY               | Add 7002-320 MOD 00, 990-E3200-002, and 3201-102H MOD 00                                  | AC-16030         |
| CA               | Add 1040-006 and 9200-0102-006  | AC-16033         |
| CB               | Add RSLM-55B/28 and 9200-0116-002   | AC-16036         |
| CC               | Add 8402-039  | AC-16038         |
| CD               | Add 1500-100 MOD 01   | AC-16039         |
| CF               | Add 6500-011 MOD 01   | AC-16041         |
| CG               | Add 8403-030 MOD 01 and 1042-021  | AC-17001         |
| CH               | Add 1801-012 and 9200-0109-112  | AC-17005         |
| CJ               | Add 7000-035, RSLM-55A/28 and 9200-0116-004   | AC-17008         |
| CK               | Add 6500-037 and 4201-100 MOD 00  | AC-17009         |
| CL               | Add 0602-002 MOD 01 and 6500-011  | AC-17010         |
| CM               | Add 8403-060 MOD 01   | AC-17011         |
| CN               | Add 8403-037 MOD 01   | AC-17012         |
| CP               | Add 9000-237 MOD 00 and 1042-004 MOD 00   | AC-17013         |
| CR               | Add 7004-363 MOD 00   | AC-17016         |

## Rosen Aviation Capability List

| Revision History |   |                  |
|------------------|---|------------------|
| Revision         | Change(s) Made                                    | Change Authority |
| CT               | Add 0603-003 MOD 02                               | AC-18018         |
| CU               | Add 1900-001 MOD 00                               | AC-18022         |
| CV               | Add SDM240-201 MOD 00                             | AC-19002         |
| CW               | Add 0700-150 MOD 05                               | AC-19004         |
| CY               | Add 2601-100 MOD 01                               | AC-19006         |
| DA               | Add 3201-100 MOD 01                               | AC-19008         |
| DB               | Add 1901-100 MOD 01 and CTS100-001 MOD 01         | AC-19009         |
| DC               | Add SDM220-001 MOD 00                             | AC-19015         |
| DD               | Add 1200-128 MOD 03 and 1200-129 MOD 03           | AC-19018         |
| DF               | Add 7001-009, 7002-126 MOD 00 and 7002-127 MOD 00 | AC-20001         |
| DG               | Add SDM260-001 MOD 00                             | AC-20002         |
| DH               | Add 3201-201 MOD 01 and SDM156-001 MOD 00         | AC-20008         |
| DJ               | Add 8403-127 MOD 01                               | AC-20010         |
| DK               | Add 1901-201 MOD 01 and SDM240-201 MOD 01         | AC-20012         |
| DL               | Add 0100-343 MOD 00                               | AC-20017         |
| DM               | Add SDM220-111 MOD 00                             | AC-20018         |
| DN               | Add 4KD240-300 MOD 00 and 441-2056-100            | AC-21001         |
| DP               | Add 9000-361 MOD 00                               | AC-21004         |
| DR               | Add 7002-361 MOD 01                               | AC-21005         |
| DT               | Add 0602-200 MOD 03                               | AC-21006         |
| DU               | Add 2002-251 and 9001901                          | AC-21008         |
| DV               | Add SDM185-001 MOD 00                             | AC-21011         |
| DW               | Add SDM320-001 MOD 00                             | AC-21012         |
| DY               | Add 990-E1010-001 and CTS100-102H MOD 00          | AC-22003         |
| FA               | Add 3201-100 MOD 00                               | AC-22004         |
| FB               | Add 2601-960 MOD 00                               | AC-22008         |